

## Extension cord for CF106 photohead

### AP10


- Standard length of cable 20m
- Standard type of cable RJ45
- It is possible to make an individual cable length - up to 100m
- Composed of AP10.T transmitter and AP10.R receiver



The AP10 extension cord is used to extend the CF106 photohead's cable. It enables to perform an error test of meter located at a considerable distance from the analyzer.

To submit a properly working set one should:

- connect AP10.R receiver with AP10.T transmitter using RJ45 cable
- connect to the AP10.T transmitter a CF106 photo head
- connect receiver AP10.R to the analyzer



Calmet sp. z o.o.  
Kukulcza 18, 65-472 Zielona Gora, Poland  
Phone +48 68 324 04 56 Fax +48 68 324 04 57  
E-mail: mail@calmet.com.pl Web access: <http://www.calmet.com.pl>